

Flexible Video-Bronchoscope







Usage

Diagnosis and treatment for bronchus

Feature

Illumination: Optical fibers

Specification

| Model: | DJF60600QG | DJF49600QG |
|---------------------------------------|-------------------|-------------------|
| Field of view: | 120° | 120° |
| Direction of view: | 0° | 0° |
| Outer diameter of insertion part (mm) | 6 mm | 4.9 mm |
| Instruments channel (mm) | 2.8 mm | 2 mm |
| Working length (mm) | 600 | 600 |
| Deepth of field (mm) | 5-50 | 5-50 |
| Bending angle | Up 180°/Down 130° | Up 180°/Down 130° |







Anti - interfere



Video Record



Vivid image



Flexible Video-Rhinolaryngoscope









Anti - interfere



Video Record



Vivid image





Usage

Diagnosis and treatment for ENT

Feature

• Illumination: Optical fibers

Specification

| Model: | DJF54360BD | DJF50360BD |
|---------------------------------------|-------------------|-------------------|
| Field of view: | 120° | 120° |
| Direction of view: | 0° | 0° |
| Outer diameter of insertion part (mm) | 3.6 | 4.9 |
| Instruments channel (mm) | / | 2.0 |
| Working length (mm) | 300 | 365 |
| Deepth of field (mm) | 5-50 | 5-50 |
| Bending angle | Up 130°/Down 130° | Up 130°/Down 130° |