

# SIDE OPEN DOOR

ROUNDFIN is committed to serving funeral industry. Provide accurate temperature control and convenient overall device for global funeral sector.

## INTRODUCTION:

ROUNDFIN focus on all-in-one funeral refrigerator which can effectively ensure temperature stability and product robustness. There are differences of 1 body to 9 bodies according to the use scene. Each room is equipped with single door& separate refrigeration compressor & separate switch which more effectively ensures the accurate temperature and save electricity.

### FEATURE:


1: The whole body is made of 304 stainless steel material.

Anti corrosion and anti rust. It is all-in-one machine without installation on-site. 2: Disposable 10 cm foam machine overall. Make cold room quickly reach the specified temperature.

- 3: LED display. Standard temperature: from 0°C to -10°C. Adjustable from -15°C to 5°C.
- 4: Separate compressor system and temperature controller system Original SECOP compressor, service life: 8-10 years.
- 5: Body tray is made of 304 stainless steel.

Capacity: 200kg, anti drop design with double rows of nylon silent rollers. Common size with Roundfin lifting trolley's tray.

- 6: Seven types of fault alarms: high temperature/low temperature/long time door opening/low voltage/sensor failure/power failure/low battery.
- 7: Each room with door locks and spare keys to ensure the safety and privacy. 8: 5 inch universal wheel for easy move.



### INSULATION TECHNOLOGY

10 cm foamed in place urethane It is a green/ environmental foam material. Disposable foam machine overall.




# COOLING QUALITY

High quality compressor (Germany Secop Compressor is optional) to be sure the necessary temperature.



### SAFETY DOOR

Safe door locked system, with lock keys. Unique door seal design for the minimum loss of cold temperature during a door opening. Door seal belt can be replaced. Door frame with a unique one-piece design.



# REMOVABLE TRAY

Separate body tray with the strong sliding system to make sure easy to pull out and pull back.Note: All the body trays (mortuary refrigerator, lifting cart, walk- in rack) size is the same.



# ALARM FUNCTION

Seven types of fault alarms: high temperature /low temperature/long time door opening/ low voltage/sensor failure/power failure/ low battery.



# UNIVERSAL WHEEL

5 inch universal wheel for easy move.14pcs maintenance free nylon roller (7pcs of each side) for easy move the body tray.





### **SPECIFICATION LIST:**

Model No.	RD-29
Material	Stainless steel 304 (201/316optional
Thickness of stainless steel	Outer:1.0 Body Tray:1.0 Inner:0.0
Compressor Place	Top of the freeze
External Size(mm)	2150*800*1750
Inner Room Size(mm)	1950*630*440
Body Tray size(mm)	1940*580
Body Tray	
Body Tray load capacity	200kg
Compressor Ge	rmany Secop/Chinese compressor(optional
Compressor Number	2 independent control of each chambe
Refrigerant	R404/
Temperature	Standard:0 to -10°C( optional -15 to 5°C
Temperature Accuracy	1°C
Working temperature	10-38°C
Foamed urethane thickness(mm)	100
Chamber Height(mm)	440
Door	
Rate of work	436W/1.2A
Voltage	220V/50HZ(110V/60HZ) optiona
Weight	280kg
Packing Size(mm)	2210*900*1810
CBM	3.0
Package	Plywood
Certification	C
Customization	All can be
III IISAGE SCENARIO-	

Model No.	RD-3S
Material	Stainless steel 304 (201/316optional)
Thickness of stainless steel	Outer:1.0 Body Tray:1.0 Inner:0.6
Compressor Place	Side of the freezer
External Size(mm)	2500*700*2030
Inner Room Size(mm)	1950*630*440
Body Tray size(mm)	1940*580
Body Tray	3
Body Tray load capacity	200kg
Compressor	Germany Secop/Chinese compressor(optional)
Compressor Number	3 independent control of each chamber
Refrigerant	R404A
Temperature	Standard:0 to -10°C( optional -15 to 5°C)
Temperature Accuracy	1°C
Working temperature	10-38℃
Foamed urethane thickness(m	nm) 100
Chamber Height(mm)	440
Door	3
Rate of work	654W/1.2A
Voltage	220V/50HZ(110V/60HZ) optional
Weight	380kg
Packing Size(mm)	2700*900*2170
CBM	5.3
Package	Plywood
Certification	CE
Customization	All can be

### **USAGE SCENARIO:**







Page 001 Page 002