200kV X-ray Machine

Directional & Glass Insert



LONG MANUFACTURING HISTORY

CINIS!

In 1964, the first portable flaw detector was born in Aolong group. Today, Aolong group has more than 50 years of manufacturing history. During this period, the design is constantly improved and innovated, the function is becoming more and more reasonable and perfect, and the quality is reliable and durable.

CAREFUL SELECTION OF PARTS

This type of portable X-ray flaw detector adopts the selected glass X-ray insert carefully. As we all know, X-ray insert is the core part of the whole set of machine. The performance and quality of the insert directly determine the quality of the whole set of machine. If the machine is used in the factory, it is more bang for the buck.

IMPROVEMENT OF MATERIAL SELECTION

In addition to the X-ray insert, the core part of the whole set of equipment is the high voltage coil. However, after the products are put on the market, there has been a dilemma that high voltage coil quality accidents occur frequently, but it can't be solved. In 2006, through the continuous exploration of engineers, we finally found the key to the quality problem of high voltage coil. The uneven diameter of enameled wire used in high voltage coil led to the damage of high voltage coil. After repeated tests, the quality problem of high voltage coil was solved after replacing the enameled wire imported from Germany.

200kV X-ray Machine

Directional & Glass Insert

SOLID AND DURABLE STRUCTURAL DESIGN

The generator of portable flaw detector isprotected by end ring,

min

Exposure chart

pramic machine: ---- Directional machine: -----

TIME SE

which is made of nearly 30mm solid steel and wrapped with rubber to prevent vibration and slipping. The end ring prevents damage to the core components in the event of a collision.

SUPER PENETRATION

A portable flaw detector equipped with the seletcted 200 kV glass X-ray insert with the beam angle of 40+5°. Under the working voltage of 200kV and focal distance of 600mm, it can penetrate 30mm Q235 steel.

POWER SUPPLY CONDITIONS

The AC-mains voltage range spans from 220 to 240 VAC and the frequency is 50Hz. The improved power factor correction module ensures stable operation, where AC-mains are unstable.

CERTIFICATES

CE (No. 3J190703.DARTQ22, Technical Construction File no. TCF-GGC-190625-064)

Verification to:


Standard: EN61010-1:2101, EN 61326-1: 2013

Related to CE Directive:

2014/35/EU (Low voltage)

2014/30/EU (Electromagnetic Compatibility)





SPECIFICATIONS FOR XXQ-2005

WEIGHT		23kg		
HEIGHT		665mm		
FOCAL SPOT SIZE EN 12543		1.5×1.5mm		
HIGH VOLTAGE ADJUSTMENT		100~200kv		
mA ADJUSTMENT		5.0mA		
MAX.PENERATION	30mm/Q235 steel	30mm/Q235 steel, 600mm focal distance		
BEAM ANGLE		40+5°		
TEMPERATURE RANGE		-10°C to +40°C		
CONT.EXPOSURE 35 C, 200kv/5.0mA		Max.5min		

MAIN CONFIGURATION

No.	Item	Specification	Qty
1	X-ray generator(with glass tube)	200kv, 5mA	1
2	Controller	T4777	1
3	Connection cables with two plugs	25m	1
4	Power supply cable with one plug	10m	1
5	Grounding cable	5m	1
6	Accessories bag		1