

Automatic Laser Particle Size Analyzer



BPSA-6100D

BPSA-5100H

BPSA-5200H

Application:

The particle size analyzer is a relatively general particle size analyzer that measures the size of powder particles according to the principle of light scattering. It has a wide dynamic range, fast measurement speed, and easy operation, making it ideal for measuring powder and liquid droplets with a wide particle size distribution. As a new type of particle size testing instrument, particle size analyzer has been widely used in other powder processing and application fields. Its application is of great significance to improve product quality and reduce energy consumption.

Features:

- * Advanced optical design: Converging Fourier transform test technology is used to ensure the maximum range of short focal lengths and effectively improve the resolution of the instrument; the uniqueness of the high-density detection unit makes it have a strong ability to detect small particles. A full range of seamless super power tests.
- * Anti dry ultrasound: ultrasonic anti-dry function can be realized to avoid damage to the ultrasonic in the absence of water.
- * Dust proof and shockproof design.
- * Sample residue-free design and bubble-free design.
- * Misoperation protection: The instrument has a self-protection function for misoperation, and the instrument does not respond to misoperation.
- * Dry Wet Switching: one button automatic switching of software.(BPSA-6100D)

Technical Parameters:

Model		BPSA-6100D		BPSA-5200H	BPSA-5100H
Test Aange		wet process: 0.01μm -1250μm	dry process: 0.1μm -1250μm	0.1μm - 800μm	0.1μm - 300μm
Test Speed		<1min/ times (excluding sample dispersion time)			
Number of Detector Channels		wet process: 112	dry process: 102	86	78
Accuracy Error		dry process: <1%, wet process: <1% (D50 value of national standard sample)		<1% (D50 value of national standard sample)	
Repeatability Error		dry process: <1%, wet process: <0.5% (D50 value of national standard sample)		<0.5% (D50 value of national standard sample)	
Wet Process	Ultrasonic	Frequency: f=40KHz, power: p=80W, time: optional, adjustable, with ultrasonic anti drying			
	Cycle and Stir	Integrated design of circular mixing, speed: 100-3950rpm, adjustable speed			Integrated design of circular mixing, speed: 10-3000rpm, adjustable speed
	Circulating Flow	Rated flow: 0-10L/min adjustable rated power: 25W			
	Sample Cell	The design of boiling type sample pool, the dispersion effect is better, capacity: 190-600mL can be normal test			
	Shading Detection	The instrument has a unique real-time detection function of the shade, to ensure that the amount of samples added more accurate			
	Dry Process	Dispersion Mode	High pressure air dispersion		
Feeding Method		Mechanical stepless speed regulation, vibration feeding, software control			
Oil Free Mute Air Compressor		With dust filtering function to ensure the accuracy of the test			
Cold Dryer		The freeze drier can filter the moisture in the air and guarantee the dispersing effect			
Power		AC220V±10%, 50/60Hz(Standard) AC110±10%, 60Hz(Optional)			
Package Size(mm)		1270*410*620 710*430*440 390*390*560 350*340*410 750*420*700 800*550*800		680*510*530	
Gross Weight(kg)		198kg		51kg	