

Class B Series



Features:

- * Built-in open type water tank
The sterilizer adopts easy-clean open type water tank which can support repeated program running if fully injected with water.
- * High-efficiency ultimate vacuum
The sterilizer adopts high-efficiency low noise vacuum system which has excellent effects.
- * Large LCD display for BKMZA/BKMZB
The LCD screen can display temperature, pressure, time, operating status, failure warning and other information. It is convenient for customers to observe the sterilizer running status.
- * Multiple program types
The system has various programs that include packed items, unpacked items, BD testing program, vacuum testing program and drying function.
- * Standard USB port for BKMZA/BKMZB
Users can store the sterilization data with USB disk.
- * Optional mini printer can be attached to record the process of sterilization.

Technical Parameters:

Model	BKMZA (Previous name: BKM-Z18B)	BKMZB (Previous name: BKM-Z24B)
Capacity	18L	23L
Chamber Size(mm)	φ247*360	φ247*470
Sterilization Class	Class B	
Sterilization Temperature	121°C, 134°C	
Drying System	Vacuum drying system	
Display	LCD display	
Testing System	B&D Test	
	Vacuum Test	
	Helix Test	
Control Precision	Temperature: 1°C	
	Pressure: 0.1bar	
Sterilization Data	BKMZA/BKMZB: USB(standard) and printer(optional)	
Safety System	Hand lock door	
	Pressure lock system	
	Relief valve in case of over pressure	
	Pressure or temperature over load protection Alarm for system failure, finish reminding, water level warning	
Water Supply System	Build-in water tank easy to clean	
Water Tank Capacity	3.5L	
Water Consumption	0.16L~0.18L in one cycle	
Tray Holder	3 pcs SS trays on SS shelf	
Chamber	SUS304	
	Max working pressure: 2.3bar	
	Min working pressure: -0.9bar Design temperature: 140°C	
Ambient Temp.	5~40°C	
Noise	<65dB	
Consumption	1950VA	1950VA
Power Supply	Standard: 220V±10%,50Hz/60Hz; Optional: 110V±10%,50Hz/60Hz. Wiring Method: Plug	
External Size(W*D*H)mm	495*600*410	495*700*410
Package Size(W*D*H)mm	610*810*590	610*810*590
Gross Weight(kg)	63	65

Note: It is applicable to the altitude below 3000 meters, and the parts need to be changed when the altitude is over 2000 meters.