

## Intermediate Frequency Therapy Instrument




BK-ZP02A

BK-ZP04A

### Features:

- \* Sp-box technology, no interference, no noise wave, pretty stable
- \* Intuitive and portable, 10.1-inch touch LCD screen
- \* 99 treatment prescriptions, 9 kinds of waveform collocation, good treatment effect
- \* Diathermy function, the temperature of electrode can be adjusted, and multiple grades available
- \* The products comply with the latest national industry standard, 2023.5.1
- \* Intelligent interaction, treatment waveform and intensity changes can be displayed at the same time



10.1-inch Touch LCD Screen

### Technical Parameters:

Model	BK-ZP02A	BK-ZP04A
Output	Double channels, two patients treated at the same time	4 channels, four patients treated at the same time
Prescriptions	99	
Modulation	0, 100%	
Carrier Frequency	2kHz, 3kHz, 4kHz, 5kHz, 10kHz	
Modulated Frequency	0~150Hz	
Current Intensity	0~100mA	
Power Supply	AC220V/110V, 50hz/60hz	
Power	90VA	
External Size(W*D*H)	340*260*125mm	288*365*995mm
Net Weight	4.4kg	22.2kg
Packing Size(W*D*H)	395*315*275mm	410*470*1130mm
Gross Weight	6.2kg	30.5kg



### Features:

- \* Diathermy function, warm heat can promote blood circulation, improve tissue metabolism, stimulate tissue regeneration, and can relieve pain and strengthen tissue nutrition.
- \* Deep penetration therapy, the intermediate frequency is up to 5kHz, which can penetrate deeper into the tissue.
- \* Four rows of digital display can display the treatment time and dose of 2 channels at the same time.
- \* The output current is less than or equal to 100mA, and 198 gears are adjustable.
- \* Synchronous and asynchronous function, 2 patients can be treated synchronously or asynchronously.
- \* Contains 29 different physiotherapy prescriptions.

### Technical Parameters:

Model	BK-MF-IIA
Output	Double channels, two patients treated at the same time
Prescriptions	29
Modulation Waveform	Square wave, trapezoidal wave, triangle wave, sawtooth wave, exponential wave, sine wave, pulse wave and other amplitude wave
Carrier Frequency	2kHz, 3kHz, 4kHz, 5kHz
Modulated Frequency	0~150Hz
Current Intensity	0~100mA
Continuous Working Time	≥4h
Modulation	0, 100%
Power Supply	AC220/110V, 50/60Hz
Power	90VA
External Size(W*D*H)	344*266*118mm
Net Weight	3kg
Packing Size(W*D*H)	470*310*260mm
Gross Weight	4.5kg