

Vertical Type Shaking Incubator



BJPX-SL10/BJPX-SL20

BJPX-SL10-L/BJPX-SL20-L

Features:

- * Large hollow electric heating perspective window, anti-condensation, convenient for customers to check the running condition of the box.
- * The display interface has the functions of historical data, curve, alarm record can be queried, data can be saved and exported, password lock screen protection and Chinese and English switching.
- * Humanized design of the door stop function, to protect the safety of personnel.
- * Box padding foot height adjustable, standard universal casters, easy to move the box.
- * Professionally designed side air vents to meet the oxygen requirement of samples.

Technical Parameters:

Model	BJPX-SL10-L	BJPX-SL10	BJPX-SL20-L	BJPX-SL20
Capacity	157L			
Display	LCD	7 inch touch screen	LCD	7 inch touch screen
Circulation Mode	Forced convection			
Shaking Mode	Rotary shaking			
Drive Mode	Three axis balanced drive type			
Vibration Range	Φ26mm			
Rotating Speed	30~300rpm			
Rotating Accuracy	±1r/min			
Temp. Range	RT+5~60℃		4~60℃	
Temp. Control Accuracy	0.1℃			
Temp. Uniformity	≤±1℃(37℃)			
Temp. Fluctuation	≤±0.5℃			
Timing Range	0~9999min(h)	0~999h59min	0~9999min(h)	0~999h59min
Shaking Plate Size	413*466mm (Two layers)			
Max. Capacity	Upper layer: 100ml*25 or 250ml*16 or 500ml*12 or 1000ml*9 (Flask clamp) Lower layer: 100ml*20 or 250ml*12 or 500ml*9 or 1000ml*6 (Flask clamp) tube rack*2 96-well plate*16 clamping rod shaking plate*2			
Standard. Capacity	Upper layer: 250ml*12 or 500ml*9 or 1000ml*6 (Flask clamp) Lower layer: Universal spring rack			
Lighting Mode	LED lamp*1			
Sterilization Mode	UV lamp*1			
Refrigerant	/		R290, 75g	
Ambient Temp.	15~35℃			
Curve Programming	Fixed value	Fixed and multi-stage	Fixed value	Fixed and multi-stage
Internal Material	304 stainless steel			
Consumption	850W		1000W	
Power Supply	AC 220V, 50/60Hz(Standard); 110V, 50/60Hz(Optional)			
Internal Size(W*D*H)	495*505*630mm			
External Size(W*D*H)	650*785*1135mm			
Package Size(W*D*H)	780*920*1290mm			
Net Weight	120kg		145kg	
Gross Weight	140kg		165kg	

Note:

1. The height of the container placed in the clamping rod shaking plate is no more than 215mm.
2. The total height of the tube placed in the tube rack is less than 160mm (if the tube has a stopper, the total height of the tube should be counted as the height of the stopper).