## Combination Emergency Shower Eye Washer



## Features:

- Features:

  \* Material: Stainless steel 304, fine polish/high brightness antioxidant coating.

  \* Assembling feature: the "Union" allows easier pipe connection and disconnection.

  \* Usage: drenching body and rinsing faces / eyes can be operated separately or simultaneously, shower & eye wash switch: two-piece ball valve.

  \* Shower head: spinning-formed with curled rim, diameter 250 mm, pipe diameter: 38 mm.

  \* Nominal pressure: 10 Mpa, working pressure: 0.2-0.4 Mpa, testing pressure: 1.5 Mpa.

  \* Flow rate of body shower: 26 Limit, flow rate of eye/face wash: ≥1.5 L/min, flow rate of eye/face wash: ≥1.5 L/min.

  \* Eyewash bow features: 300 mm in diameter.

  \* Inlet height(From above the floor): 1186 mm, outlet height(From above the floor): 86 mm, distance between spray heads: 170 mm, water pattern coverage: at the height of 1520 mm above floor, the water pattern coverage: at the height of 1520 mm above floor, the water pattern coverage: at the height of 1520 mm above floor, the water pattern coverage: at the height of 1520 mm above floor, the water pattern coverage: at the height of 1520 mm above floor, the water pattern coverage: at the height of 1520 mm above floor, the water pattern coverage: at the height of 1520 mm above floor, the water pattern coverage: at the height of 1520 mm above floor.

# Technical Parameters:

Model	SEW-C1	SEW-C2	
Package Size(W*D*H)	1310*380*250mm	1310*350*440mm	
Gross Weight	17.5kg	20kg	

## Fiber Analyzer



ive UI enabling one-hand op		
ive UI enabling one-hand op		
	eration.	
ocols.		
password or fingerprint login		
can be assigned a customiz		
		cyclee
	COTOSION, SELVICE IIIE OVEL 10,000	cycles.
	d leakage.	
equired, odor-free.		
pid, uniform heating.		
	ooling water.	
	en limits are exceeded.	
utomatic result printing after	sample mass input.	
BK-F1600		
Room temperature ~100°C	Sample Batch Capacity	1~24
).5~1.5g	Adding Method	Manual
0.1~100%	Temperature Control Accuracy	±0.2℃
0~999min		
If the fiber content is less than 10%, the relative deviation is ≤5%;		
If the fiber content is greater than 10%, the relative deviation is <3%		
24~96 pieces of crude fiber, 24~120 pieces of neutral detergent fiber/acid		
detergent fiber/lignin(8-hour working system)		
560*430*510mm		
28kg		
660*500*590mm		
14ka		
	s, on-screen status display is, on-screen status display is pressure and are).  uturing operation, alarm for ili pull in the properties of the status of the	s; on-screen status display for quick maintenance, perature, high pressure and corrosion; service life over 10,000 are).  uturing operation; alarm for lid leakage, equired, odor-free, equired, equire

503 504