

Shoe Cover Dispenser



BK-SCD-W



BK-SCD-WH

Introduction:

This device automatically dispenses disposable shoe covers to maintain cleanliness. It is essential for preventing contamination in critical environments such as hospital cleanrooms, electronics factories, food processing plants, laboratories, and modern residential or commercial entrances.

Features:

- * It is equipped with a digital display, malfunction warnings, and automatic recovery from power-on/off cycles.
- * Fits all types of men's and women's shoes. When stepping into the machine, the support hooks automatically close, ensuring that stepping down is always smooth and the shoe cover never gets stuck.
- * Four pairs of infrared sensors are installed on both sides of the stepping well, providing full-range detection to ensure user safety.
- * The hooks that open the shoe covers feature a hidden design. There is no horizontal bar moving back and forth across the stepping well, so even if the machine malfunctions, it will not cause any harm to the foot.
- * LED lights intelligently guide the user through the process of wearing the shoe covers.

Technical Parameters:

Model	BK-SCD-W	BK-SCD-WH
Dispensing Speed	3 seconds per shoe cover	
Armrest	Without	Included
Max Capacity	PE shoe covers: 200pcs/box Non-woven shoe covers: 100pcs/box	
Standard Accessory	PE shoe covers: 200pcs/box(A free substitution with non-woven shoe covers can be requested by adding a remark to your order)	
Optional Accessory	Shoe covers	
Power Supply	AC 110/220V, 50/60Hz	
Internal Operating Voltage	DC 12V, 6A	
External Size(W*D*H) (Including standard shoe covers)	630*310*1010mm	
Package Size(W*D*H) (Including standard shoe covers)	710*375*1070mm	
Net Weight(Including standard shoe covers)	20kg	21kg
Gross Weight(Including standard shoe covers)	22kg	23kg
Package Size(W*D*H)	PE shoe covers: 800*475*600mm (200pcs/box, 21boxes/case, 4200pcs total) Non-woven shoe covers: 800*490*630mm (100pcs/box, 21boxes/case, 2100pcs total)	
Gross Weight	PE/Non-woven shoe covers: 15kg	

Note: Must use genuine manufacturer-specific shoe covers.