



To become the world famous brand of dental equipment, to become the domestic and foreign dentists respect and praise of the enterprise

COMPANY PROFILE

Foshan wenjian medical Co., Ltd. was established in 2006, is located in Guangdong province oral medical device base shishan Town foshan City Nanhai District Xiaode Lake Park, elegant environment, convenient transportation.

The main business is high speed and low speed dental handpiece, and the first one in China to achieve the standardization of dental handpiece, mold and automatic production, dental handpiece is the largest capacity, the largest market sales, the best after-sales service of professional manufacturers.

The main products cover restoration, implant, root canal, orthodontics and other categories. In recent years, with advanced technical means and advantages in product structure, we have successively developed non-retractive high-speed dental handpiece, ultra-high torque implant handpiece, clinical low-voltage electric micromotor, ultra-long life 1:5 increasing contra angle, endomotor and other products (see product atlas for details). With advanced research and development concept, exquisite technology, efficient management, excellent quality, we have already got ISO13485, CE certification, FDA certification of the United States, South Korea GMP certification and a number of national patent certification, products sold in more than 100 countries and regions.



CONTENTS

01 01-----04

IMPLANT

02 05-----14

HIGH
SPEED HANDPIECE

03 15-----22

LOW
SPEED HANDPIECE

04 23-----26

ELECTRIC MOTORS

05 27-----27

LIGHT CURING

06 28-----28

ROOT CANAL

07 29-----32

MISCELLANEOUS

08 33-----40

ACCESSORIES

QUALIFICATION AND HONOR



Three certificates displayed in a row:

- 医疗器械生产许可证** (Medical Device Production License)
- 高新技术企业证书** (High-Tech Enterprise Certificate)
- 营业执照** (Business License)



Six certificates displayed in a row, all titled **中华人民共和国医疗器械注册证** (People's Republic of China Medical Device Registration Certificate).



5⁺
INVENTION
PATENT

20⁺
**APPEARANCE DESIGN
PATENT CERTIFICATE**

IMPLANT UV ACTIVATOR

-  Fast healing time
-  Closed to save
-  Anti-infection device



Implant UV
activator interface



Before use



After use


- ⦿ Catalytic improvement of planting surface in 15 minutes
- ⦿ 360° no dead angle catalysis

YWJ-QSY001

- Input power
AC100-240V 50/60Hz
- Output power
5V-6A.24V-3A



MONITOR OSSEOINTEGRATION (ISQ)



WJ-DC-001

- Input power
5VDC 1VA
- Charger input
5V

Accurately measure the stability of the
implant through digital quantification




IMPLANT
CONTRA ANGLE

WJ-422



Number	120104	120103	120102
Ratio	20:1	20:1	20:1
Noies	≤ 60db	≤ 60db	≤ 60db

IMPLANT
TRAY




- 150017 L
- 150018 M
- 150019 S

IMPLANT
TORQUE HANDLE



Number	120098
Torque gear	20N/35N
Wrench size	1.2mm

FIERI SERIES HANDPIECE



● Head anti-back suction design, prevent dirt from entering the head of the machine and cartridge, longer service life.



Number	110451 (R1)	110429 (F2)
Bur applicabie	φ1.595mm-φ1.600mm	φ1.595mm-φ1.600mm
Air pressure	0.25mpa-0.30mpa	30mpa-40mpa
Rotation speed	320.000rpm-420.000rpm	320.000rpm-420.000rpm
Noies	≤ 63db	≤ 63db

HIGH SPEED COLOR HANDPIECE WJ-122/124

● Beautiful appearance,aluminum alloy, lightweight,various color,you use different colors of handpiece according to customers preferences, suit for female doctors.



Number	— — —
Bur applicabie	φ1.595-φ1.600mm
Air pressure	0.25mpa-0.30mpa
Rotation speed	280.000-400.000RPM
Noies	≤ 65db

HIGH SPEED HANDPIECE WITH ANTI-SUCTION SYSTEM




WJ-122/124

✓ Aiti-Retractio



Number	110469	110059
Bur applicabie	φ1.595-φ1.600mm	φ1.595-φ1.600mm
Air pressure	0.25mpa-0.30mpa	0.25mpa-0.30mpa
Rotation speed	280.000-400.000RPM	280.000-400.000RPM
Noies	≤ 65db	≤ 65db


ANTI-RETRACTION HANDPIECE



WJ-122/124



LED E-GENERATOR HANDPIECE



WJ-162/164

- Self-illuminated, natural Led light
- 2 hole , 4 hole universally , can be use without fiber optic system
- It can be autoclaved repeatedly
- Three water spray , better atomization,comprehensive cooling cutting surface



Number	110236	110232	110218
Bur applicabie	φ1.595-φ1.600mm	φ1.595-φ1.600mm	φ1.595-φ1.600mm
Air pressure	0.25mpa-0.30mpa	0.25mpa-0.30mpa	0.25mpa-0.30mpa.0
Rotation speed	280.000-400.000RPM	280.000-400.000RPM	280.000-400.000RPM
Noies	≤ 65db	≤ 65db	≤ 65db

45 DEGREE SURGICAL HANDPIECE

WJ-162/164



Number	110181	110056
Bur applicabie	φ1.595-φ1.590mm	φ1.595-φ1.590mm
Air pressure	0.25mpa-0.30mpa	w.25mpa-0.30mpa
Rotation speed	380.000-420.000RPM	380.000-420.000RPM
Noies	≤ 65db	≤ 65db

CLOSE TYPE HANDPIECE SERIES




WJ-112/114
WJ-132/134



Number	110001	110011
Bur applicabie	φ1.595-φ1.600mm	φ1.595-φ1.600mm
Air pressure	0.25mpa-0.30mpa	w.25mpa-0.30mpa
Rotation speed	280.000-400.000RPM	280.000-400.000RPM
Noies	≤ 65db	≤ 65db

U TYPE E-GENERATOR LED HANDPIECE




WJ-164



Number	110253	110223
Bur applicabie	φ1.595-φ1.600mm	φ1.595-φ1.600mm
Air pressure	0.25mpa-0.30mpa	0.25mpa-0.30mpa
Rotation speed	280.000-400.000RPM	280.000-400.000RPM
Noies	≤ 65db	≤ 65db

U TYPE E-GENERATOR LED HANDPIECE




WJ-164



Nsk type quick coupling E-generator LED handpiece


WJ-162/164



110561	110350	10172	110051
φ1.595-φ1.600mm	φ1.595-φ1.600mm	φ1.595-φ1.600mm	φ1.595-φ1.600mm
0.25mpa-0.30mpa	0.25mpa-0.30mpa	0.25mpa-0.30mpa	0.25mpa-0.30mpa.0
280.000-400.000RPM	280.000-400.000RPM	280.000-400.000RPM	280.000-400.000RPM
≤ 65db	≤ 65db	≤ 65db	≤ 65db

FIBER OPTIC HIGH SPEED HANDPIECE

WJ-164




- Using fiber optic, come with open type cartridge, easy to change bearing
- Unique lamp cap design,easy to change bulb not easy to break
- Triple water spray, cooling at all direction
- Quick coupler, easy operation



Number	110264	110262	110258
Bur applicabie	φ1.595-φ1.600mm	φ1.595-φ1.600mm	φ1.595-φ1.600mm
Air pressure	0.25mpa-0.30mpa	0.25mpa-0.30mpa	0.25mpa-0.30mpa.0
Rotation speed	280.000-400.000RPM	280.000-400.000RPM	280.000-400.000RPM
Noies	≤ 65db	≤ 65db	≤ 65db

EXTERNAL SERIES



WJ-414/412



Number	120038	120050	120056	120069
Ratio	1:1	1:1	1:1	1:1
Air pressure	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa
Rotation speed	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM
Noies	≤ 68db	≤ 68db	≤ 68db	≤ 68db

WJ-412/414 EXTERNAL SERIES



Number	120032	120034	120030	120028
Ratio	1:1	1:1	1:1	1:1
Air pressure	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa
Rotation speed	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM
Noies	≤ 68db	≤ 68db	≤ 68db	≤ 68db

EXTERNAL SERIES WJ-412/414



Number	120164	120133	120134
Ratio	1:1	1:1	1:1
Air pressure	0.30mpa-0.35mpa	0.30mpa-0.35mpa	w0.30mpa-0.35mpa
Rotation speed	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM
Noies	≤ 68db	≤ 68db	≤ 68db

WJ-424/422 INTERNAL SERIES



Number	120092	120084	120089	120082
Ratio	1:1	1:1	1:1	1:1
Air pressure	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa
Rotation speed	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM
Noies	≤ 68db	≤ 68db	≤ 68db	≤ 68db

INTERNAL SERIES WJ-424/422




Number	120090	120094	120091	120097
Ratio	1:1	1:1	1:1	1:1
Air pressure	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa
Rotation speed	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM	≥ 15.000RPM
Noies	≤ 68db	≤ 68db	≤ 68db	≤ 68db

REDUCTION
HANDPIECE SERIES WJ-422



Number	120100 (10:1)	120101 (16:1)	120105 (64:1)
Ratio	10:1	16:1	64:1
Air pressure	0.30mpa-0.35mpa	0.30mpa-0.35mpa	0.30mpa-0.35mpa
Noies	≤ 60db	≤ 60db	≤ 60db

ORTHDONTICS
CONTRA ANGLE WJ-422



Number	120014 (1:1)	120123 (4:1)
Air pressure	0.30mpa-0.35mpa	0.30mpa-0.35mpa
Noies	≤ 65db	≤ 65db



BRUSHLESS CLINICAL MICROMOTOR

- 输入电源 Input power
DC 24V
- 转速 Rotation speed
2000-40000rpm
- 扭矩 Torque
3.4Ncm
- 噪音 Noise level
<60dB



WJ-60A
Number: 130002

Size of motor Weight of motor Illuminate
φ22xL71 mm 71g LED(white light)

INCREASING CONTRA ANGLE (1:5/1:4.2)

WJ-422



编 号 Number	120104 (1:1)	120010 (1:5)	15015 (1:4.2)
工作气压 Air pressure	0.20mpa-0.25mpa	0.20mpa-0.25mpa	0.20mpa-0.25mpa
噪 音 Noies	≤ 63db	≤ 63db	≤ 63db
速 比 Ratio	1: 1	1: 5	1: 4.2

LABORATORY SERIES




Number	130021
Rotation speed	35,000rpm
Input power	220V/110V
Noies	≤ 65db

- 01 WJ-90
130021
- 02 WJ-90-204
130009
- 03 WJ-90-102-317
—

- 04 WJ-90-102
130003
- 05 WJ-90-18
130004

PORTABLE MICRO MOTOR



Number	120104
Rotation speed	2000-40000rpm
Torque	3.4Ncm
Input power	DC24V
Noies	≤ 60db

CURING LIGHT



- One second light curing, the light intensity can reach 1600mw/cm2
- Wireless charging function,microcomputer
- Handheld design

RESIN



·Replaceable metal light guide rod (direct head)



EMDO MOTOR



Number	120016
Battery voltage	3.7Vdc
Battery capacity	800mAh
Rated input voltage	Ac100~240V 60/60Hz
Output voltage	5vdc
Output current	1A
Speed range(rpro)	130-600
Ratio	16:1
Torque(N.cm)	0.6-3.0

DENTAL COMPOSITE HEATER

WJ-JRQ



Number	150036
Input	100-240V AC 50/60Hz 0.8A Max
Output	12V DC 2A
Power	24W
Temperature setting	40±1℃、50±1℃、70±℃

ORTHODONTIC SCREW DNVER



- WJ-414Z 01
150015 (LONG)
- WJ-414Z 02
150016 (SHORT)

SAND BLASTING UNIT

WJ-PSQ



Number	150038
Air pressure	0.30mpa-0.40mpa
Spray Hole	φ0.5mm

COLORFUL 3 WAY
SYRINGE

WJ-183C



Number 150002 150005 150008 150003

COLORFUL 3 WAY
SYRINGE

WJ-183B




Number 150001






















Number WJ-YP0476-2




























ALUMINIUM OXIDE











WJ-YP0476







DIAMOND BURS

FG. 314 Medium ISO No. 806.314.524 标准粒度 蓝色圈	 ISO 001/008 0.8/19.0 BR-49	 ISO 001/010 1.0/19.0 BR-45	 ISO 001/012 1.2/19.0 BR-46	 ISO 001/014 1.4/19.0 BR-41	 ISO 001/016 1.6/19.0 BR-40	 ISO 001/018 1.8/19.0 BR-31	 ISO 001/020 2.0/19.0 BR-28	 ISO 001/023 2.3/19.0 BR-26	 ISO 001/025 2.5/19.0 BR-25	 ISO 001/029 2.9/19.0 BR-23	 ISO 002/012 2.3/19.0 BC-43
	Order No. 001-008M	001-010M	001-012M	001-014M	001-016M	001-018M	001-020M	001-023M	001-025M	001-029M	002-012M
 ISO 002/014 2.3/19.0 BC-42	 ISO 002/016 2.5/19.0 BC-32	 ISO 002/018 2.5/19.0 BC-31	 ISO 010/010 1.0/19.0 SI-45	 ISO 010/012 1.2/19.0 SI-46	 ISO 010/014 1.6/19.0 SI-47	 ISO 010/016 1.8/19.0 SI-48	 ISO 019/010 3.2/19.0 DI-41	 ISO 019/014 3.2/19.0 DI-42	 ISO 038/032 5.0/19.0 EX-11	 ISO 039/035 7.0/20.0 EX-12	 ISO 041/025 0.5/19.0 WF-30
002-014M	002-016M	002-018M	010-010M	010-012M	010-014M	010-016M	019-010M	019-014M	038-032M	039-035M	041-025M
 ISO 042/040 2.0/19.0 WR-45	 ISO 042/050 2.0/19.0 WR-46	 ISO 055/045 2.0/19.0 WR-44	 ISO 068/042 1.8/19.0 WR-13	 ISO 109/010 4.0/19.0 SF-41	 ISO 109/012 4.0/19.0 SF-31	 ISO 109/014 4.0/19.0 SF-42	 ISO 110/014 6.0/21.0 SF-21	 ISO 110/016 6.0/21.0 SF-15	 ISO 111/012 8.0/22.0 SF-11	 ISO 111/014 8.0/22.0 SF-12	 ISO 111/016 8.0/22.0 SF-13
042-040M	042-050M	055-045M	068-042M	109-010M	109-012M	109-014M	110-014M	110-016M	111-012M	111-014M	111-016M
 ISO 138/010 4.0/19.0 SR-41	 ISO 138/012 4.0/19.0 SR-31	 ISO 138/014 4.0/19.0 SR-42	 ISO 140/014 6.0/21.0 SR-21	 ISO 141/012 8.0/22.0 SR-11	 ISO 141/014 8.0/22.0 SR-12	 ISO 141/016 8.0/22.0 SR-13	 ISO 150/012 0.2/21.0 EX-18	 ISO 164/012 6.0/21.0 TC-26	 ISO 165/014 8.0/22.0 TC-21	 ISO 166/014 10.0/24.0 TC-10	 ISO 166/016 10.0/24.0 TC-11
138-010M	138-012M	138-014M	140-014M	141-012M	141-014M	141-016M	150-012M	164-012M	165-014M	166-014M	166-016M
 ISO 166/018 10.0/24.0 TC-16	 ISO 169/010 3.0/19.0 TF-41	 ISO 170/012 4.0/19.0 TF-42	 ISO 170/014 4.0/19.0 TF-43	 ISO 170/016 4.0/19.0 TF-31	 ISO 171/014 6.0/21.0 TF-20	 ISO 171/016 6.0/21.0 TF-21	 ISO 171/018 6.0/21.0 TF-23	 ISO 171/021 6.0/21.0 TF-22	 ISO 172/010 8.0/22.0 TF-07	 ISO 172/012 8.0/22.0 TF-08	 ISO 172/014 8.0/22.0 TF-09
166-018M	169-010M	170-012M	170-014M	170-016M	171-014M	171-016M	171-018M	171-021M	172-010M	172-012M	172-014M
 ISO 172/016 8.0/22.0 TF-10	 ISO 172/018 8.0/22.0 TF-56	 ISO 172/023 9.0/22.0 TF-14	 ISO 173/014 10.0/24.0 TF-11	 ISO 173/016 10.0/24.0 TF-12	 ISO 173/018 10.0/24.0 TF-13	 ISO 196/010 4.0/19.0 CR-41	 ISO 196/012 4.0/19.0 CR-31	 ISO 196/014 4.0/19.0 CR-42	 ISO 196/016 4.0/19.0 CR-12	 ISO 196/020 5.0/19.0 CR-11	 ISO 197/014 6.0/21.0 TR-20
172-016M	172-018M	172-023M	173-014M	173-016M	173-018M	196-010M	196-012M	196-014M	196-016M	196-020M	197-014M


											
197-016M	197-018M	197-020M	198-014M	198-016M	198-018M	199-014M	199-016M	199-018M	199-022M	200-022M	200-024M
											
225-014M	225-018M	233-010M	234-014M	237-018M	237-021M	237-032M	248-012M	248-014M	249-014M	249-016M	250-012M
											
257-018M	257-023M	257-028M	257-032M	277-020M	277-030M	288-012M	289-014M	304-023M	304-038M	304-050M	515-014M
	FG. 314 Super Coarse ISO No. 806.314.544 特粗粒度 黑色圈										
519-016M	Order No.	001-014S	001-016S	001-018S	001-020S	010-016S	038-032S	039-035S	109-012S	109-014S	111-014S
											
111-016S	166-016S	166-018S	171-016S	173-014S	173-016S	173-018S	197-016S	199-014S	199-016S	199-018S	237-018S
						FG. 314 Coarse ISO No. 806.314.534 较粗粒度 绿色圈					
277-020S	198C-016S	198C-021S	508T-014S	508T-016S	508T-021S	Order No.	001-018C	010-014C	068-042C	111-014C	165-014C
					FG 314 Fine ISO No. 806.314.514 较细粒度 红色圈						
173-018C	190-018C	197-018C	199-018C	257-018C	Order No.	001-008F	150-012F	165-014F	166-016F	171-016F	173-014F

											
173-016F	196-016F	196-020F	197-014F	197-016F	197-018F	199-014F	199-016F	199-018F	234-014F	237-021F	249-014F
			FG. 314 Extra Fine ISO No. 806.314.504 特细粒度 黄色圈								
249-016F	254-016F	289-014F	Order No.	001-016EF	165-014EF	166-016EF	171-016EF	173-014EF	173-016EF	196-016EF	196-020EF
											
197-016EF	197-018EF	199-014EF	199-016EF	199-018EF	237-021EF	243-010EF	248-012EF	248-014EF	249-014EF	249-016EF	254-016EF








RA / CA shank 204 弯机头金刚石车针 $\varnothing 2.3mm$ 22mm

RA / CA 204 Coarse ISO No. 806.204.534 较粗粒度 绿色圈				RA / CA 204 Medium ISO No. 806.204.524 标准粒度 蓝色圈							
Order No.	001-R014C	001-R016C	001-R023C	Order No.	001-R010M	001-R012M	001-R014M	001-R016M	001-R023M	010-R010M	010-R012M
											
010-R014M	010-R016M	109-R010M	109-R012M	111-R012M	141-R012M	141-R014M	165-R014M	166-R016M	198-R018M	199-R016M	225-R014M
			RA / CA 204 Fine Grit ISO No. 806.204.514 较细粒度 红色圈								
225-R018M	257-R018M	257-R028M	Order No.	001-R016F	001-R023F	165-R014F	257-R018F				

FG S Short shank 313 / 短柄金刚石车针总长, 16mm Ø1.6mm

FG Short medium ISO No. 806.313.524 FG短柄 标准粒度 蓝色圈											
	ISO 001/010 1.0/16.0	ISO 001/014 1.4/16.0	ISO 010/012 1.3/16.0	ISO 010/016 1.8/16.0	ISO 165/014 8.0/19.0	ISO 170/010 3.0/16.0	ISO 170/016 4.0/16.0	ISO 171/014 6.0/18.0	ISO 171/018 6.0/17.0	ISO 197/016 6.0/17.0	ISO 249/014 8.0/19.0
Order No.	001-S010M	001-S014M	010-S012M	010-S016M	165-S014M	170-S010M	170-S016M	171-S014M	171-S018M	197-S016M	249-S014M

FG XL extra long shank 316 / 加长金刚石车针, 总长25mm Ø1.6mm

FG XL 316 Extra Long Standard 806.316.524 加长柄 标准粒度 蓝色圈											
	ISO 001/010 1.0/25.0	ISO 001/012 1.2/25.0	ISO 001/014 1.4/25.0	ISO 001/016 1.6/25.0	ISO 001/018 1.8/25.0	ISO 001/021 2.1/25.0	ISO 010/012 1.2/25.0	ISO 042/040 2.0/25.0	ISO 055/045 2.0/25.0	ISO 110/014 6.0/27.0	ISO 111/012 8.0/28.0
	BR-X45	BR-X46	BR-X41	BR-X40	BR-X31	BR-X28	SI-X46	WR-X45	WR-X44	SF-X21	SF-X11
	Order No.	001-X010M	001-X012M	001-X014M	001-X016M	001-X018M	001-X021M	010-X012M	042-X040M	055-X045M	110-X014M
											
ISO 111/014 8.0/28.0	ISO 111/016 8.0/28.0	ISO 165/014 8.0/28.0	ISO 166/016 10.0/29.0	ISO 173/014 10.0/29.0	ISO 173/016 10.0/29.0	ISO 173/018 10.0/29.0	ISO 198/018 8.0/28.0	ISO 199/016 10.0/29.0	ISO 200/022 11.5/29.0	ISO 225/014 4.0/25.0	ISO 249/014 8.0/28.0
SF-X12	SF-X13	TC-X21	TC-X11	TF-X11	TF-X12	TF-X13	TR-X23	TR-X12	TR-X15	SI-X50	FO-X21
111-X014M	111-X016M	165-X014M	166-X016M	173-X014M	173-X016M	173-X018M	198-X018M	199-016XLM	200-X022M	225-X014M	249-X014M
				FG XL 316 Extra Long Super Coarse 806.316.544 加长柄 特粗粒度 黑色圈						FG XL 316 Extra Long Coarse 806.316.534 加长柄 较粗粒度 绿色圈	
ISO 249/016 8.0/28.0	ISO 257/018 3.6/25.0	ISO 515/014 8.0/28.0	ISO 519/016 8.0/28.0			ISO 001/018 1.8/25.0	ISO 001/021 2.1/25.0	ISO 055/045 2.0/25.0	ISO 173/016 10.0/29.0	ISO 001/014 1.4/25.0	ISO 001/016 1.6/25.0
FO-X22	FO-X32	BC-X11	BC-X12			BR-X31S	BR-X28S	WR-X44S	TF-X12S	BR-X41C	BR-X40C
249-X016M	257-X018M	515-X014M	519-X016M	Order No.	001-X018S	001-X021S	055-X045S	173-X014S	Order No.	001-X014C	001-X016C
											
ISO 001/018 1.8/25.0	ISO 001/021 2.1/25.0	ISO 055/045 2.0/25.0	ISO 165/014 8.0/28.0	ISO 173/016 10.0/29.0							
BR-X31C	BR-X28C	WR-X44C	TC-X21C	TF-X12C							
001-X018C	001-X021C	055-X045C	165-X014C	173-X016C							


Push Button open type cartridge series

	WJ-G4-QQ-T2		WJ-G2-QQ-T2		WJ-G3-Q3-MX
	WJ-F4-PP-T2		WJ-F2-PP-T2		WJ-F3-P3-MX





Anti-retraction open type cartridge series

	WJ-G4-QQ-T2-D		WJ-G2-QQ-T2-D		WJ-G3-Q3-MX-D
	WJ-F4-PP-T2-D		WJ-F2-PP-T2-D		WJ-F3-P3-MX-D


Wrench chuck type open type cartridge series

	WJ-G4-WW-T2		WJ-G2-WW-T2		WJ-G3-W3-MX
	WJ-F4-WW-T2		WJ-F2-WW-T2		WJ-F3-W3-MX

Push Button close type cartridge series

	WJ-E1-PP-T2		WJ-E2-P2-A6		WJ-E3-P3-MX
	WJ-D1-PP-T2		WJ-D2-P2-A6		WJ-D3-P3-MX

Push Button close type cartridge series




Other accessories



Shaft accessories



Head accessories



Other accessories



Quick coupling



Quick coupling



BUSINESS COVERAGE

150020-25 Our company has always passed ISO13485, FDA and CE certifications and a number of national patent certifications. Various products are exported to more than 100 countries and regions in the world including India, Turkey, Egypt, Iran, Germany, the United States, Japan, South Korea, Hong Kong, Brazil, Venezuela, South Africa and so on.

01

pre-sale service

- Professional consulting
- product description
- professional service

02

In-sale service

- High efficiency production
- Transport coordination
- Specialized market dynamic guidance

03

After-sales service

- Regular visit
- Regular maintenance

